

# FPX-1FRH08240

---



FPX Fiber Optic Termination Panel with HMFOC tether, 1RU, 19in, Singlemode, 24 fiber, LC/UPC Connector to 2x12 fiber HMFOC, putty white

## Product Classification

<b>Regional Availability</b>	Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber patch panel
<b>Product Series</b>	FPX

## General Specifications

<b>Functionality</b>	Patching
<b>Adapter Packs Included, quantity</b>	2
<b>Body Style</b>	Symmetrical
<b>Color</b>	Putty white
<b>Color, front</b>	Putty white
<b>Growth Configuration</b>	Partially loaded
<b>Interface, front</b>	LC
<b>Interface Feature, front</b>	Standard
<b>Patching Capacity, maximum</b>	24
<b>Rack Type</b>	EIA 19 in   EIA 23 in
<b>Rack Units</b>	1
<b>Shelf Movement</b>	Sliding
<b>Total Fibers, quantity</b>	24
<b>Total Ports, quantity</b>	24

## Dimensions

<b>Height</b>	44.45 mm   1.75 in
<b>Width</b>	482.6 mm   19 in
<b>Depth</b>	304.8 mm   12 in
<b>Cable Stub Length</b>	0 m   0 ft

## Material Specifications

# FPX-1FRH08240

---

**Finish** Powder coated

**Material Type** Steel

## Optical Specifications

**Fiber Mode** Singlemode

## Environmental Specifications

**Operating Temperature** -40 °C to +85 °C (-40 °F to +185 °F)

**Storage Temperature** -40 °C to +85 °C (-40 °F to +185 °F)

## Packaging and Weights

**Included** Mounting hardware

**Packaging quantity** 1