

# FGS-HNTS-H-12MM-A

---



FiberGuide® Top Support Adjustable C-Bracket Kit, 12mm for 4x24in System

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Support mounting kit
<b>Product Brand</b>	FiberGuide®
<b>Product Series</b>	FGS

## General Specifications

<b>Product Feature</b>	Adjustable Height
<b>Color</b>	Black
<b>Orientation</b>	Horizontal
<b>Section Type</b>	Bracket

## Dimensions

<b>Height</b>	307.34 mm   12.1 in
<b>Width</b>	57.912 mm   2.28 in
<b>Length</b>	715.01 mm   28.15 in
<b>Thread Size</b>	12 mm
<b>System Dimensions</b>	102 mm x 610 mm (4 in x 24 in)

## Ordering Tree

# FGS-HNTS-H-12MM-A

FGS -  -  -  -  -  -  -

## For Section Size

9	empty	4 x 4 in, 4 x 6 in
	F	4 x 12 in

## For Threaded Rod Size

10	1/2	1/2 in
	1/2-LP	1/2 in, low profile
	12MM	12 mm
	12MM-LP	12 mm, low profile
	14MM	14 mm
	14MM-LP	14 mm, low profile
	16MM	16 mm
	16MM-LP	16 mm, low profile
	5/8	5/8 in
	5/8-LP	5/8 in, low profile

11	A	Adjustable
----	---	------------

## Material Specifications

**Material Type** Carbon steel

## Packaging and Weights

**Included** Hardware

**Packaging quantity** 1

**Weight, net** 3.289 kg | 7.25 lb