

# CB-LH-25

---



Locking Heads for Cable Banding CB-12-50, 25 pcs (uses CB-IT installation tool - not incl)

## Product Classification

<b>Product Type</b>	Banding
<b>Ordering Note</b>	CommScope® standard product in the United States and Canada

## General Specifications

<b>Adapter Type</b>	Adapter
<b>Color</b>	Black
<b>Mounting</b>	Round member

## Dimensions

<b>Height</b>	12.446 mm   0.49 in
<b>Width</b>	19.05 mm   0.75 in
<b>Length</b>	0.021 m   0.07 ft

## Material Specifications

<b>Material Type</b>	Heat-stabilized weather resistant acetal
----------------------	--

## Environmental Specifications

<b>Operating Temperature</b>	-65 °C to +90 °C (-85 °F to +194 °F)
------------------------------	--------------------------------------

## Packaging and Weights

<b>Packaging quantity</b>	25
---------------------------	----

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CSA	Compliant

# CB-LH-25

---

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

