

# CLT5XM-CO

## Base Product



MQ Multiport cluster 5 ports cable assembly with interface type MQ female to Nex10 male, size 1/4"

## Product Classification

<b>Product Type</b>	Wireless transmission cable assembly
<b>Product Series</b>	MQ
<b>Warranty</b>	Two years

## General Specifications

<b>Attachment, Connector A</b>	Factory attached
<b>Attachment, Connector B</b>	Factory attached
<b>Body Style, Connector A</b>	Straight
<b>Body Style, Connector B</b>	Straight
<b>Interface, Connector A</b>	MQ Female
<b>Interface, Connector B</b>	NEX10 Male
<b>Specification Sheet Revision Level</b>	A

## Dimensions

<b>Nominal Size</b>	1/4 in
---------------------	--------

## Port Configuration

Pin Assignment	Label
1	MQ5-1 (R+)
2	MQ5-2 (CR+)
3	MQ5-3 (CL+)
4	MQ5-4 (L+)
5	MQ5-5 (CAL)

# CLT5XM-CO

---

## Mechanical Specifications

**Minimum Bend Radius, multiple Bends** 25.4 mm | 1 in

**Minimum Bend Radius, single Bend** 25.4 mm | 1 in

## Environmental Specifications

**Operating Temperature** -40 °C to +85 °C (-40 °F to +185 °F)

**Immersion Test Method** IEC 60529, IP67

## \* Footnotes

**Warranty** For more information, please consult our Product Warranty guidelines