# 760253784 | WMFE2-S211-N-00



Wall Mountable Fiber Endclosure including 1 SC/APC adapter and 1 900µ pigtail, feeder cable can be stored up to 50m depending cable diameter, cable cover not included

#### **Product Classification**

Regional Availability EMEA

PortfolioCommScope®Product TypeFiber wall box

Product Series WMFE

## General Specifications

**Adapter Ports, quantity** 

Adapters, quantity 2

Cable Entry Location Bottom

**Color** Light Gray (RAL 7035)

Interface SC/APC

Mounting Wall mount

Patch Cord Routing Downward

Patching Capacity, maximum 4
Splicing Capacity, maximum 4

Splicing Type SMOUV

#### **Dimensions**

 Height
 196 mm | 7.717 in

 Height, with cover
 mm | 11.063 in

 Width
 154 mm | 6.063 in


 Depth
 43 mm | 1.693 in


 Outer Cable Diameter
 10 mm | 0.394 in

## Dimension Drawing



# 760253784 | WMFE2-S211-N-00





# **Environmental Specifications**

Flammability Rating UL 94 V-0

UV Resistance UV stabilized

### Packaging and Weights

 Height, packed
 44 mm | 1.732 in

 Width, packed
 156 mm | 6.142 in

 Depth, packed
 286 mm | 11.26 in

Packaging quantity 24

Packaging Type Carton

**Weight, gross** 0.513 kg | 1.131 lb

### Regulatory Compliance/Certifications

# Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



