760253785 | WMFE2-S202-N-00



Wall Mountable Fiber Endclosure including 2 SC/APC adapters and no 900µ pigtails, feeder cable can be stored up to 50m depending cable diameter, cable cover not included

Product Classification

Regional Availability EMEA

Portfolio CommScope®
Product Type Fiber wall box

Product Series WMFE

General Specifications

Adapter Ports, quantity

Adapters, quantity 2

Cable Entry Location Bottom

Color Light Gray (RAL 7035)

Interface SC/APC

Mounting Wall mount

Patch Cord Routing Downward

Patching Capacity, maximum 4
Splicing Capacity, maximum 4

Splicing Type SMOUV

Dimensions

 Height
 196 mm | 7.717 in

 Height, with cover
 mm | 11.063 in

 Width
 154 mm | 6.063 in


 Depth
 43 mm | 1.693 in


 Outer Cable Diameter
 10 mm | 0.394 in

Dimension Drawing



760253785 | WMFE2-S202-N-00





Environmental Specifications

Flammability Rating UL 94 V-0

UV Resistance UV stabilized

Packaging and Weights

 Height, packed
 44 mm | 1.732 in

 Width, packed
 156 mm | 6.142 in

 Depth, packed
 286 mm | 11.26 in

Packaging quantity 24

Packaging Type Carton

Weight, gross 0.513 kg | 1.131 lb