

# HFT410-1SBVYF-G



HELIAX® Hybrid Cable Assembly, BiDi, 6-OVP box to RRU, UL Type TC-ER, 4 power conductors 10 AWG at OVP, 2 power cords 8 AWG at RRU, 1 Simplex fiber connectors, FullAXS, PVC jacket, aluminum armor, OVP gland insert kit included

## Product Classification

<b>Regional Availability</b>	North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Hybrid cable assembly
<b>Product Brand</b>	HELIAX®
<b>Product Series</b>	HFT
<b>Ordering Note</b>	CommScope® non-standard product

## General Specifications


<b>Conductors, quantity</b>	4
<b>Construction Type</b>	Hybrid standard tail
<b>Interface, Connector A</b>	LC
<b>Interface Feature, connector A</b>	Outdoor
<b>Interface Body Style, connector A</b>	Straight
<b>Interface, Connector B</b>	LC
<b>Interface Feature, connector B</b>	Standard
<b>Interface Body Style, connector B</b>	Straight
<b>Jacket Color</b>	Black
<b>Total Fibers, quantity</b>	1

## Dimensions

<b>Cable Assembly Length Range (ft)</b>	3 – 400
<b>Diameter Over Jacket</b>	18.31 mm   0.721 in

## Ordering Tree

# HFT410-1SBVYF-G



## Mechanical Specifications

**Minimum Bend Radius** 221 mm | 8.701 in

## Optical Specifications

**Fiber Type** G.657.A2

**Insertion Loss, typical note** Insertion loss is measured at 1310 and 1550 nm

**Insertion Loss, typical** 0.5

## Environmental Specifications

**Operating Temperature** -40 °C to +75 °C (-40 °F to +167 °F)

## Packaging and Weights

**Cable weight** 0.5 kg/m | 0.336 lb/ft

## \* Footnotes

**Insertion Loss, typical note** Insertion loss is measured at a room temp of +20°C (+68°F)