

# VZWSMART-SFK3 | V-BRACING KIT



## V-BRACING KIT

V-Bracing Kit for Tower with saddle clamps for 1.5"- 8-5/8" OD or 8" 60 degree angle or 6" 90 degree angle Tower legs, Dual Pivoting Angle Arms, 96" long, attaches up to 4-1/2" OD horizontals

## Product Classification

<b>Product Type</b>	Reinforcement kit
<b>Ordering Note</b>	CommScope® non-standard product

## General Specifications

<b>Mounting</b>	Angle 60°, 203.2 mm (8 in)   Angle 90°, 152.4 mm (6 in)   Round member   Straight or tapered legs up to 203.2 mm (8 in) OD
<b>Pipe, quantity</b>	0
<b>Tower Taper</b>	Non-tapered   Tapered

## Dimensions

<b>Mounting Diameter 2, maximum</b>	114.3 mm   4.5 in
<b>Mounting Diameter, maximum</b>	203.2 mm   8 in
<b>Mounting Diameter, minimum</b>	38.1 mm   1.5 in

## Material Specifications

<b>Material Type</b>	Hot dip galvanized steel
----------------------	--------------------------

## Packaging and Weights

<b>Included</b>	Clamps   Legs   Saddle mount
<b>Packaging quantity</b>	1

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

# VZWSMART-SFK3 | V-BRACING KIT

---

