

# F1A-HMHF-P-SGW

---

## Base Product



FSJ1-50A SureFlex® Jumper with interface types 4.3-10 Male and 4.3-10 Female with HELIAX® SureGuard weatherproofing, (boot on HM end only)

## Product Classification

<b>Product Type</b>	Wireless transmission cable assembly
<b>Product Series</b>	FSJ1-50A

## General Specifications

<b>Attachment, Connector A</b>	Factory attached
<b>Attachment, Connector B</b>	Factory attached
<b>Body Style, Connector A</b>	Straight
<b>Body Style, Connector B</b>	Straight
<b>Interface, Connector A</b>	4.3-10 Male
<b>Interface, Connector B</b>	4.3-10 Female
<b>Specification Sheet Revision Level</b>	A

## Dimensions

<b>Cable Assembly Length Range (m)</b>	1 – 15
<b>Nominal Size</b>	1/4 in

## Electrical Specifications

<b>3rd Order IMD Static</b>	-110 dBm
<b>3rd Order IMD Static Test Method</b>	Two +43 dBm carriers

## Jumper Assembly Sample Label

# F1A-HMHF-P-SGW

---



## Environmental Specifications

**Immersion Test Method**

Meets IEC 60529:2001, IP68 in mated condition

**Weatherproofing Method**

HELIAX® SureGuard weatherproofing boot