

F042KMS5



FlexTwist® Flexible Twist for WR42, 17.7–26.5 GHz, with interface types PBR220 and UBR220, 1200 mm

Product Classification

Product Type	Rectangular waveguide, flexible twist
Product Brand	FlexTwist®

General Specifications

Component	Flexible Twist
Interface	PBR220
Interface 2	UBR220

Dimensions

Length	1200 mm 47.244 in
Waveguide Size	WR42 WG20 R220

Electrical Specifications

Attenuation	2.62 dB/m 0.799 dB/ft
Average Power	100 W
Operating Frequency Band	17.7 – 26.5 GHz
Peak Power	39 kW
VSWR	1.35

Mechanical Specifications

Minimum Bend Radius, Multiple Bends (E Plane)	38 mm 1.496 in
Minimum Bend Radius, Multiple Bends (H Plane)	76 mm 2.992 in
Maximum Twist	510 °/m 155.448 °/ft
Pressurization, maximum	0.31 N/mm ² 45 psi

F042KMS5

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

