

# MC-CGC12M-B



3-Sector Cage Mount Monopole Platform Base Kit w/ Equip Rig Point, 12 in to 50 in OD, 12 ft 6 in face, pipe ordered separately

## OBSOLETE

This product was discontinued on: December 12, 2022

### Replaced By:

MC-PM12M-BC

ATLAS 12 ft Monopole Platform with Top Rail Kit. Antenna Pipe Sold Separately.

## Product Classification

**Product Type** Co-location platform

## General Specifications

**Mounting** Monopole, 304.8–1270 mm (12–50 in) OD

**Pipe, quantity** 0

**Sectors, quantity** 3

## Dimensions

**Height** 3048 mm | 120 in

**Face Width** 3.81 m | 12.5 ft

**Width** 3810 mm | 150 in

**Face Support Pipe Diameter** 73.66 mm | 2.9 in

**Mounting Diameter, maximum** 1270 mm | 50 in

**Mounting Diameter, minimum** 304.8 mm | 12 in

**Pipe Outer Diameter** 73.66 mm | 2.9 in

## Material Specifications

**Material Type** Hot dip galvanized steel

# MC-CGC12M-B

---

## Mechanical Specifications

<b>Wind Rating</b>	For Specifications, please contact <a href="mailto:steelproducts@commscope.com">steelproducts@commscope.com</a> or call 800-255-1479
<b>Wind Rating Test Method</b>	TIA/EIA-222

## Packaging and Weights

<b>Included</b>	Pipe mounts   Platform   Rail   Ring mount
<b>Packaging quantity</b>	1
<b>Weight, net</b>	656.348 kg   1447 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



## \* Footnotes

<b>Wind Rating</b>	BWS—Base Wind Speed; FBC—Florida Building Code
--------------------	--