

# LSX-LM1242-A-SPL

---



LSX Fiber Termination/Splice Panel 8 Ru, 288 - LC/APC, Singlemode Stranded

## Product Classification

<b>Regional Availability</b>	Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber patch/splice panel
<b>Product Series</b>	LGX

## General Specifications

<b>Functionality</b>	Patching   Splicing
<b>Application</b>	Used in LSX-style frames only
<b>Cable Stub Type</b>	Pigtails, stranded
<b>Color</b>	Putty white
<b>Color, front</b>	White
<b>Growth Configuration</b>	Fully loaded
<b>Interface, front</b>	LC/UPC
<b>Rack Type</b>	EIA 23 in
<b>Rack Units</b>	8
<b>Shelf Movement</b>	Fixed
<b>Splicing Type</b>	Heat shrink, single fiber fusion
<b>Total Ports, quantity</b>	288

## Dimensions

<b>Height</b>	279.4 mm   11 in
<b>Width</b>	482.6 mm   19 in
<b>Depth</b>	381 mm   15 in

# LSX-LM1242-A-SPL

---

## Material Specifications

**Finish** Powder coated

**Material Type** Steel

## Optical Specifications

**Fiber Mode** Singlemode

## Packaging and Weights

**Included** Mounting hardware

**Packaging quantity** 1