

# MC-DPM3-84

---



GroundSmart® Monopole Co-location Dual Pipe Mount Kit, 4 ft 9 in face, includes pipe

## Product Classification

**Product Type** Co-location dual pipe mount kit

## General Specifications

**Pipe, quantity** 2

**Sectors, quantity** 1

## Dimensions

**Height** 2,133.6 mm | 84 in

**Face Width** 1.463 m | 4.8 ft

**Width** 1,447.8 mm | 57 in

**Length** 355.6 mm | 14 in

**Pipe Length** 2,133.6 mm | 84 in

**Pipe Outer Diameter** 73.66 mm | 2.9 in

**Stand-off Distance** 355.6 mm | 14 in

## Material Specifications

**Material Type** Hot dip galvanized steel

## Mechanical Specifications

**Wind Rating** 120 mph (BWS) at 150 ft AGL | 140 mph (3-second gust) at 150 ft AGL using Exposure D per FBC

**Wind Rating Criteria** Four 72 in x 8 in panel antennas per sector

**Wind Rating Test Method** TIA/EIA-222-G

## Packaging and Weights

**Included** Dual pipe frames | Pipe mounts

**Packaging quantity** 1

**Weight, net** 80.195 kg | 176.8 lb

# MC-DPM3-84

---

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

### \* Footnotes

<b>Wind Rating</b>	BWS—Base Wind Speed; FBC—Florida Building Code
--------------------	--