


MC-HP12S-B



3-Sector Monopole Co-location Platform Base Kit, 10 in to 30 in OD, 12 ft 6 in face, pipe ordered separately

OBSOLETE

This product was discontinued on: **March 9, 2022**

Replaced By:

MC-HP12M-B

3-Sector Monopole Co-location Platform Base Kit, 12 in to 50 in OD, 12 ft 6 in face, pipe ordered separately

Product Classification

Product Type Monopole platform kit

General Specifications

Mounting Monopole, 254–762 mm (10–30 in) OD

Pipe, quantity 0

Sectors, quantity 3

Dimensions

Face Width 3.81 m | 12.5 ft

Width 3810 mm | 150 in

Mounting Diameter, maximum 762 mm | 30 in

Mounting Diameter, minimum 254 mm | 10 in

Pipe Outer Diameter 60.96 mm | 2.4 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating 120 mph (BWS) at 100 ft AGL | 140 mph (3-second gust) at 150 ft AGL using Exposure D per FBC

Wind Rating Test Method TIA/EIA-222

MC-HP12S-B

Packaging and Weights

Included	Platform Rail Ring mount
Packaging quantity	1
Weight, net	813.291 kg 1793 lb

* Footnotes

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code