

7845389-1032 | UAP2 7E/17E/19/37T F-DC



Carrier Access Point with MIMO 2x2 Radio Module for Low Power USA 700, USA 750, LMR 750, AWS 1700, PCS 1900, and C-Band TDD Applications, Fiber fed, DC

Product Classification

Product Type	Access point
Product Brand	ERA®
Product Series	UAP2

General Specifications

Antenna Type	MIMO Antenna
Fan Kit	Included
Fed Type	Fiber fed
Note	Detailed Product Specifications are available. Please contact your local CommScope representative.
Power Class	Low
Powering Type	External DC powered

Electrical Specifications

License Band	AWS 1700 C-Band LMR 750 PCS 1900 USA 700 USA 750
Voltage Range	-57 to -42 Vdc

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

