760254513 | EPX-3U-SPL-ENC



EPX 3U Splicing Fiber Panel accepts up to 7 EPX splice trays providing up to 336 single fiber splicing or up to 1008 ribbon fiber splicing

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber splice panel
Product Series	EPX

General Specifications

Color	Black
Interface, front	Unloaded
Rack Units	3
Shelf Movement	Sliding
Total Ports, quantity	0

Dimensions

Height	177 mm 6.969 in
Width	482.6 mm 19 in
Depth	434.1 mm 17.091 in

Environmental Specifications

Flammability Rating

UL 94 V-0

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

Page 1 of 2

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: January 16, 2025



760254513 | EPX-3U-SPL-ENC



Page 2 of 2

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: January 16, 2025

