



Indoor/Outdoor Low Smoke Zero Halogen, TeraSPEED® Tight Buffered Office Distribution Fiber Fiber Optic Cable, 12 fiber, Singlemode OS1a, black. Provides Rodent Resistance.

- designed to offer flexibility, strength and compact construction for internal and interbuilding use
- non-metallic construction reinforced by E-glass yarns, which provide rodent resistance and higher tensile strength
- oversheathed with a ULSZH jacket meeting IEC fire performance requirements

## Product Classification

<b>Regional Availability</b>	Asia   EMEA
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber indoor/outdoor cable
<b>Product Series</b>	C-DS

## General Specifications

<b>Cable Type</b>	Tight buffer
<b>Jacket Color</b>	Black
<b>Jacket Marking</b>	Meters
<b>Jacket Marking Method</b>	Inkjet
<b>Jacket Marking Text</b>	COMMSCOPE GB OPTICAL CABLE 760254801 12 X 9/125 OS2 ULSZH (BATCH NUMBER) (METRE MARK)
<b>Strength Members</b>	E-glass yarns
<b>Fibers per Subunit, quantity</b>	12
<b>Total Fiber Count</b>	12

## Dimensions

<b>Diameter Over Jacket</b>	8 mm   0.315 in
-----------------------------	-----------------

## Representative Image



## Mechanical Specifications

<b>Minimum Bend Radius, loaded</b>	200 mm   7.874 in
<b>Minimum Bend Radius, unloaded</b>	120 mm   4.724 in
<b>Tensile Load, short term, maximum</b>	1500 N   337.214 lbf
<b>Cable Crush Resistance, maximum</b>	20 N/mm   114.203 lb/in

## Optical Specifications

<b>Fiber Type</b>	OS2
-------------------	-----

## Optical Specifications, Wavelength Specific

<b>Standards Compliance</b>	IEC 60794-1   TIA-492CAAB (OS2)
-----------------------------	---------------------------------

## Environmental Specifications

<b>Installation temperature</b>	-5 °C to +50 °C (+23 °F to +122 °F)
<b>Operating Temperature</b>	-20 °C to +60 °C (-4 °F to +140 °F)
<b>Storage Temperature</b>	-20 °C to +60 °C (-4 °F to +140 °F)
<b>EN50575 CPR Cable EuroClass Fire Performance</b>	Cca
<b>EN50575 CPR Cable EuroClass Smoke Rating</b>	s2
<b>EN50575 CPR Cable EuroClass Droplets Rating</b>	d1
<b>EN50575 CPR Cable EuroClass Acidity Rating</b>	a1
<b>Environmental Space</b>	Low Smoke Zero Halogen (LSZH)

## Packaging and Weights

### Cable weight

69 kg/km | 46.366 lb/kft

## Regulatory Compliance/Certifications

### Agency

### Classification

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

ROHS

Compliant

UK-ROHS

Compliant



## Included Products

CS-8W-TB - TeraSPEED® Singlemode Fiber

## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable