

# PGP-CS12

---



Polymer PIM-Guard Antenna and RRU Cable Support Bracket with 12 positions / 24 cables for stackable hangers (up to 2 per position)

Compatible with first and second generation Polymer PIM-Guard products

-SSH-1416

-SSH-411

-SSH-1117

## Product Classification

<b>Product Type</b>	Support bracket
<b>Product Brand</b>	PIM-Guard

## General Specifications

<b>Cable Runs, quantity</b>	12
<b>Hole, quantity</b>	12
<b>Mounting</b>	Round member


## Dimensions

<b>Height</b>	50.8 mm   2 in
<b>Width</b>	304.8 mm   12 in
<b>Length</b>	304.8 mm   12 in
<b>Mounting Diameter, maximum</b>	76.2 mm   3 in
<b>Mounting Diameter, minimum</b>	60.96 mm   2.4 in
<b>Hole Size</b>	3/4 in

## Ordering Tree

# PGP-CS12

---



## Material Specifications

**Material Type** Polymer

## Packaging and Weights

**Packaging quantity** 1

**Weight, net** 0.93 kg | 2.05 lb

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

