

CSC4-MBA1A1BB011



NOVUX™ CSC100 Compact Fiber Closure, splice only Single circuit Module, no splitters, mounting clips, grey, no drop CR

- CommScope's new NOVUX™ non-hardened compact closure designed for the drop (access) network
- Configurable as splice only or connectorized solution
- Octopus™ gel compatible with high end environmental specifications for aerial, pedestal, underground and direct buried applications
- Available in black (RAL 9005) and gray (RAL 7035)
- NOVUX™ compact closures come with a QR code link to product documentation and C-track
- Modular design compatible with a range of accessories such as mounting brackets, cable retentions, grounding, etc.
- Removable inner body with 360-degree access for ease of fiber installation

Product Classification

Regional Availability	Asia EMEA Latin America North America
Portfolio	CommScope®
Product Type	Single-ended, rectangular fiber closure
Product Brand	NOVUX™
Product Series	CSC 100

General Specifications

Cable Ports Quantity, total	3 round ports + 6 multi-out ports (12 cables)
Cable Sealing Type	Compressed gel
Closure Sealing Type	Hinged with latch
Closure Style	Single-ended
Color	Gray
Mounting	Pole Wall
Port Type	No adapter
Port, quantity	0
Splitter Type	No splitter
Splitter, quantity	0

Dimensions


Height	284 mm 11.181 in
---------------	--------------------

CSC4-MBA1A1BB011

Width 117 mm | 4.606 in
Depth 77 mm | 3.031 in

CSC4-MBA1A1BB011

Dimension Drawing




Port Configuration

Position	Cable diameter	
	mm	Inches
Feeder cable	≤ 14	≤ 0.55
Branch cable	≤ 12	≤ 0.47
Single drops	≤ 8 (flat cable: 8 x 4,5)	≤ 0.32 (flat cable: 0.32 x 0.18)
Dual drops	≤ 6,2	≤ 0.25

Ordering Tree

CSC4-MBA1A1BB011



Environmental Specifications

Environmental Space	Outdoor
UV Resistance	UV stabilized

Packaging and Weights

Included	Mounting hardware
Packaging quantity	1
Packaging Type	Box Carton