760255037 | WMFE2-S211-C-00



Wall Mountable Fiber Endclosure including 1 SC/APC adapter and 1 900µ pigtail, feeder cable can be stored up to 50m depending cable diameter, cable cover included

Product Classification

Regional Availability	EMEA
Portfolio	CommScope®
Product Type	Fiber wall box
Product Series	WMFE

General Specifications

Adapter Ports, quantity	
Adapters, quantity	2
Cable Entry Location	Bottom
Color	Light Gray (RAL 7035)
Interface	SC/APC
Mounting	Wall mount
Patch Cord Routing	Downward
Patching Capacity, maximum	4
Splicing Capacity, maximum	4
Splicing Type	SMOUV
Dimensions	
Height	196 mm 7.717 in
Height, with cover	mm 11.063 in

Width	154 mm 6.063 in
Depth	43 mm 1.693 in
Outer Cable Diameter	10 mm 0.394 in


Dimension Drawing


Page 1 of 2

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 25, 2023



760255037 | WMFE2-S211-C-00





Environmental Specifications

Flammability Rating	UL 94 V-0
UV Resistance	UV stabilized

Packaging and Weights

Height, packed	55 mm 2.165 in
Width, packed	156 mm 6.142 in
Depth, packed	286 mm 11.26 in
Packaging quantity	24
Packaging Type	Carton
Weight, gross	0.55 kg 1.213 lb

Page 2 of 2

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 25, 2023

