



G2 Splice Cassette, 12LC/UPC with internal shutters, OS2, with pigtails, Method B Enhanced

For use in applications when End B of the cable is connectorized with an MPO that connects into a module with Method B Enhanced polarity

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber cassette with pigtails
<b>Product Series</b>	G2

## General Specifications

<b>Color, front</b>	Blue
<b>Interface, front</b>	LC/UPC
<b>Interface, rear</b>	Stranded pigtail
<b>Polarity</b>	Method B Enhanced
<b>Shuttered</b>	Yes
<b>Total Fibers, quantity</b>	12

## Dimensions

<b>Height</b>	26.416 mm   1.04 in
<b>Width</b>	96.52 mm   3.8 in
<b>Depth</b>	165.354 mm   6.51 in

## Material Specifications

<b>Alignment Sleeve Material</b>	Zirconia
----------------------------------	----------

## Optical Specifications

<b>Fiber Mode</b>	Singlemode
-------------------	------------

# 760255886 | G2-SP-12LCG-PT-BE

---

<b>Fiber Type</b>	G.657.A2
<b>Insertion Loss, maximum</b>	0.25 dB
<b>Return Loss, minimum</b>	50 dB

## Environmental Specifications

<b>Qualification Standards</b>	IEC 61753-1   TIA-568.3-D
<b>Safety Standard</b>	UL

## Packaging and Weights

<b>Included</b>	SMOUV holder   SMOUV splice protection
<b>Packaging quantity</b>	1
<b>Weight, net</b>	0.126 kg   0.278 lb