MUK-MSK7 | PIPE TO ANGLE CROSSOVER KIT



Pipe to Angle Cross Over Plate, Mounts up to 4-1/2" Pipe to Angled member, Pipe/Angle not included

| Product Classification | |
|------------------------------------|--------------------------|
| Product Type | Clamp plate |
| General Specifications | |
| Mounting | Crossover plate |
| Dimensions | |
| Mounting Diameter, maximum | 114.3 mm 4.5 in |
| Material Specifications | |
| Material Type | Hot dip galvanized steel |
| | |
| Environmental Specifications | |
| EPA with 1/2 in (12 mm) radial ice | ft² |
| Packaging and Weights | |
| Included | Clamp assembly |
| Packaging quantity | 1 |
| * Footnotes | |

EPA with 1/2 in (12 mm) radial ice EPA-Effective Projected Area

Page 1 of 1

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 26, 2024

