

# MUK-SFK1 | TIE BACK ASSEMBLY

---



Tieback Bracket / Stiff Arm, 2-3/8" OD x 12 ft Pipe with Attachment Hardware, for 1-1/2" to 8" OD or 60 degree angle tower leg

## Product Classification

**Product Type** Stiff arm mount

## General Specifications

**Mounting** Round and angle legs

**Pipe, quantity** 1

## Dimensions

**Pipe Length** 3,048 mm | 120 in

**Pipe Outer Diameter** 60.325 mm | 2.375 in

## Material Specifications

**Material Type** Hot dip galvanized steel

## Packaging and Weights

**Included** Attachment hardware | Pipe

**Packaging quantity** 1

## Included Products

SA-B – Stiff Arm /Tieback Brackets for 2-3/8 in OD pipe - Pipe not included



## Stiff Arm /Tieback Brackets for 2-3/8 in OD pipe - Pipe not included

### Product Classification

**Product Type** Stiff arm mount

### General Specifications

**Mounting** Round and angle legs

**Pipe, quantity** 0

### Dimensions

**Height** 152.4 mm | 6 in

**Width** 203.2 mm | 8 in

**Length** 203.2 mm | 8 in

**Mounting Diameter, maximum** 88.9 mm | 3.5 in

**Mounting Diameter, minimum** 48.26 mm | 1.9 in

### Material Specifications

**Material Type** Hot dip galvanized steel

### Packaging and Weights

**Included** Attachment hardware | Brackets

**Packaging quantity** 1

**Weight, net** 8.301 kg | 18.3 lb

### Regulatory Compliance/Certifications

#### Agency

CHINA-ROHS

ISO 9001:2015

#### Classification

Below maximum concentration value

Designed, manufactured and/or distributed under this quality management system

# SA-B

---

ROHS

Compliant

UK-ROHS

Compliant

