

# 760255079 | PPL-SP-12LC-SM-RPT-AS



Propel Singlemode Splice Cassette, 12LC/UPC with internal shutters, OS2 ribbon fiber pigtail, pairs straight ULL

- Can be installed and removed from front or rear of panel
- This component requires 3 of the 12 lanes on the Propel Panel blade

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	SYSTIMAX®
<b>Product Type</b>	Fiber cassette with ribbon pigtail
<b>Product Brand</b>	Propel
<b>Product Series</b>	PPL

## General Specifications

<b>Color, front</b>	Blue
<b>Interface, front</b>	LC/UPC
<b>Interface, rear</b>	Stranded pigtail
<b>Polarity</b>	Pairs, straight
<b>Shuttered</b>	Yes
<b>Total Fibers, quantity</b>	12

## Dimensions

<b>Height</b>	67.31 mm   2.65 in
<b>Width</b>	97.993 mm   3.858 in

## Optical Specifications

<b>Fiber Mode</b>	Singlemode
<b>Fiber Type</b>	G.657.A2
<b>Insertion Loss, maximum</b>	0.25 dB

## Environmental Specifications

<b>Qualification Standards</b>	IEC 61753-1   TIA-568.3-D
<b>Safety Standard</b>	UL

## Packaging and Weights

**Included** Single Fusion Splice Protection Sleeves

**Packaging quantity** 1

## Included Products

FST-ACC006 – Fiber Optic Protective Splice Sleeve, 12f mass fusion, 5 pack