



Propel Singlemode Splice Cassette, 12LC/APC with internal shutters, OS2 ribbon fiber pigtail, Method B Enhanced ULL

- Can be installed and removed from front or rear of panel
- This component requires 3 of the 12 lanes on the Propel Panel blade

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	SYSTIMAX®
<b>Product Type</b>	Fiber cassette with ribbon pigtail
<b>Product Brand</b>	Propel
<b>Product Series</b>	PPL

## General Specifications

<b>Color, front</b>	Green
<b>Interface, front</b>	LC/APC
<b>Interface, rear</b>	Ribbon pigtail
<b>Polarity</b>	Method B Enhanced (ULL)
<b>Shuttered</b>	Yes
<b>Total Fibers, quantity</b>	12

## Dimensions

<b>Height</b>	67.31 mm   2.65 in
<b>Width</b>	97.993 mm   3.858 in

## Optical Specifications

<b>Fiber Mode</b>	Singlemode
<b>Fiber Type</b>	G.657.A2
<b>Insertion Loss, maximum</b>	0.25 dB

## Environmental Specifications

<b>Qualification Standards</b>	IEC 61753-1   TIA-568.3-D
<b>Safety Standard</b>	UL

## Packaging and Weights

<b>Included</b>	Single Fusion Splice Protection Sleeves
<b>Packaging quantity</b>	1