

CLICK-SERIES-HANGERS

Base Product



CLICK-Series Click-on Hangers

Product Classification

Product Type	Hanger kit
Product Brand	HELIAX®

General Specifications

Color	Black
Hanger Type	Click-on hanger

Material Specifications

Material Type	Engineered plastic
----------------------	--------------------

Mechanical Specifications

Vibration Survival	≥4 hours at resonant frequency
---------------------------	--------------------------------

Environmental Specifications

Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
Environmental Strength Capability	Double cable weight
UV Resistance, minimum with no degradation	≥100 hours exposure in accelerated UV life chamber