760255955 | PPL-4U-W



Propel 4RU sliding tray white fiber panel, accepts Propel ULL modules or adapter packs, providing up to 288 duplex LC ports, 288 MPO ports or 576 SN ports (1152f)

- Any size Propel component can be used in each panel or blade
- Components can be installed and removed from front or rear of panel
- Supports 8f, 12f, 16f and 24f applications while maintaining full panel density
- Cable mounting system allows for multiple trunk cables to be securely attached in the rear of panel

Product Classification

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio SYSTIMAX®

Product Type Fiber patch panel

Product Brand Propel
Product Series PPL

General Specifications

Color Gray

Interface, front Unloaded

Rack Type EIA 19 in

Rack Units 4

Shelf Movement Sliding

Dimensions

 Height
 178 mm
 | 7.008 in

 Width
 483 mm
 | 19.016 in

 Depth
 470 mm
 | 18.504 in



760255955 | PPL-4U-W

Port Configuration

Panel				
size	8-fiber components	12-fiber components	16-fiber components	24-fiber components
1RU	up to 6 per blade	up to 4 per blade	up to 3 per blade	up to 2 per blade
2RU	up to 6 per blade	up to 4 per blade	up to 3 per blade	up to 2 per blade
4RU	up to 6 per blade	up to 4 per blade	up to 3 per blade	up to 2 per blade
Each blade has 12 lanes				
	Requires 2 lanes	Requires 3 lanes	Requires 4 lanes	Requires 6 lanes

Material Specifications

Material Type Steel

Environmental Specifications

Safety Standard c-UL-us

Packaging and Weights

Packaging quantity

Weight, net 14.742 kg | 32.5 lb