# NG4-SPLICE-TRAYS



### NG4access® Splice Tray

The NG4 Splice trays hold up to six mass fusion protection sleeves for 72-fiber capacity or up to 24 single fusion protection sleeves. Each tray provides for storage of 6 feet of jacketed cable and an additional 3 feet of unjacketed fiber inside the tray.

The NG4 splice chassis installs on the back side of the NG4access frame below the bottom horizontal trough and holds up to 48 splice trays. The single fusion splice tray has a maximum capacity of 24 fibers for 1152 fiber maximum capacity per chassis. The ribbon splice tray has a maximum capacity of 72 fibers for 3456 fiber maximum capacity per chassis. Pigtail 24-fiber microcable cabled modules connect any universal chassis to the splice chassis

#### Product Classification

Regional Availability Latin America | North America

Product Type Fiber splice tray

Product Brand NG4access®

Product Series NG4

### General Specifications

**Application** Used in NG4access-style frames only

**Color** Black

**Splicing Type** Heat shrink, single fiber fusion | Mass fusion

#### Dimensions

 Height
 148 mm | 5.827 in

 Width
 191 mm | 7.52 in

 Depth
 19 mm | 0.748 in

## Packaging and Weights

Packaging quantity

