

MC-PK10-DSH



Low-Profile Co-location Platform Kit for 15in to 50in OD Monopoles, 10 ft face, (9) 2-7/8" OD x 96" Pipes, with Support Rail Kit

Please contact ANDREW for detailed drawings prior to ordering.

Product Classification

Product Type	Monopole platform kit
Ordering Note	ANDREW® non-standard product
Warranty	One year

General Specifications

Mounting	Monopole, 381–1270 mm (15–50 in) OD
Pipe, quantity	9
Sectors, quantity	3

Dimensions

Height	2,438.4 mm 96 in
Face Width	3.048 m 10 ft
Width	3,810 mm 150 in
Pipe Length	2,438.4 mm 96 in
Face Support Pipe Diameter	88.9 mm 3.5 in
Mounting Diameter, maximum	1,270 mm 50 in
Mounting Diameter, minimum	381 mm 15 in
Pipe Outer Diameter	73.025 mm 2.875 in
Stand-off Distance	1,117.6 mm 44 in

Material Specifications

Material Type	Hot dip galvanized steel
----------------------	--------------------------

Mechanical Specifications

Wind Rating	For Specifications, please contact your local ANDREW representative
Wind Rating Test Method	TIA/EIA-222

MC-PK10-DSH

Packaging and Weights

Included	Hardware Plain end pipes (9) Platform Rail Ring mount
Packaging quantity	1
Weight, net	833.703 kg 1838 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



* Footnotes

Warranty	For more information, please consult our Product Warranty guidelines
Wind Rating	BWS—Base Wind Speed; FBC—Florida Building Code