


# MC-PM10M4-16-126

---



Atlas 4-Sector Monopole Platform Base kit, 15 in to 45 in OD, 2-7/8 in OD x 10 ft 6 in face & (16) 2-7/8 in OD x 126 in antenna pipes. Top rail ordered separately.

## Product Classification

<b>Product Type</b>	Monopole platform kit
<b>Product Series</b>	ATLAS

## General Specifications

<b>Pipe, quantity</b>	16
<b>Sectors, quantity</b>	4

## Dimensions

<b>Face Width</b>	3.2 m   10.5 ft
<b>Pipe Length</b>	3,200.4 mm   126 in
<b>Face Support Pipe Diameter</b>	73.025 mm   2.875 in
<b>Mounting Diameter, maximum</b>	1,143 mm   45 in
<b>Mounting Diameter, minimum</b>	381 mm   15 in
<b>Pipe Outer Diameter</b>	73.025 mm   2.875 in

## Material Specifications

<b>Material Type</b>	Hot dip galvanized steel
----------------------	--------------------------

## Mechanical Specifications

<b>Wind Rating</b>	For Specifications, please contact <a href="mailto:steelproducts@commscope.com">steelproducts@commscope.com</a> or call 800-255-1479
<b>Wind Rating Test Method</b>	TIA/EIA-222

## Packaging and Weights

<b>Included</b>	Plain end pipes   Platform   Ring mount
-----------------	---

# MC-PM10M4-16-126

---

**Packaging quantity** 1  
**Weight, net** 1,219.12 kg | 2,687.7 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



## \* Footnotes

**Wind Rating** BWS—Base Wind Speed; FBC—Florida Building Code