

4




3

2

1

- 1.0 GENERAL NOTES
 - 1.1 ALL METRIC DIMENSIONS ARE IN BRACKETS [X.X]
 - 1.2 FEATURES CRITICAL TO QUALITY ARE INDICATED IN ROUNDED BOX (XX)
 - 1.3 3D DIGITAL FILES ARE FOR REFERENCE. IN CASE OF CONFLICT FOLLOW PDF DRAWING.
- 2.0 DESIGN NOTES
 - 2.1 ALL BENDS SHALL HAVE A BEND RADIUS OF $\geq 1X$ MATERIAL THICKNESS, UNLESS OTHERWISE SPECIFIED
- 3.0 MANUFACTURING/SPECIAL REQUIREMENTS
 - 3.1 BREAK SHARP EDGES AND DEBURR PART FOR SAFE HANDLING
 - 3.2 GALVANIZE PER ASTM A123
 - 3.3 MARK WITH PART NUMBER, REVISION, AND VENDOR ID WITH ETCH, STAMP OR LABEL. CHARACTERS TO BE 0.12" TO 0.24" HIGH AND LEGIBLE TO THE UNAIDED EYE.
- 4.0 TEST
- 5.0 PACKAGING
 - 5.1 PACKAGING SHALL MEET COMMSCOPE REQUIREMENTS PER DOCUMENT IS-PL-3005

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	RY1002 30NOV23	YZ1080 40184296CMO



COMMSCOPE, INC. OF NORTH CAROLINA											
TOLERANCES					SAP MATERIAL MASTER						
1 PLACE .X[X] ± 0.1[3.0]			3 PLACE .XXX[X] ± 0.030[0.8]		WB-CY212						
2 PLACE .XX[X] ± 0.06[1.5]			ANGLES ± 1°								
FINISH GALV A123					MATERIAL A568						
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES INTERPRET PER ANSI Y 14.5M-1994	NAME		DATE		SAFETY GRATING, 24"X144"						
	CE	RY1002	30NOV23								
	RW	RY1002	12/21/2023								
	AD	YW1045	01/02/2024								
	RE	YMENG	01/02/2024								
ECN 40184296CMO					SCALE 1:12		DOCUMENT NO. WB-CY212				
SIZE		Auth Group		INSL		MODEL			DRAWING		
C						VERSION	STATUS	REVISION	VERSION	STATUS	REVISION
						00	RE	A	00	RE	A
SHEET 1 OF 1											

DENSITY	0.28	lbs/in³
MASS	96.36	lbs
VOLUME	338.91	in³
SURFACE AREA	6022.06	in²
HEIGHT	3.0"	
LENGTH	144.0"	
WIDTH	24.0"	