



Outdoor Fiber Cable, 48-fiber, singlemode OS2, loose tube s/sheath, black

## Product Classification

|                              |                       |
|------------------------------|-----------------------|
| <b>Regional Availability</b> | Australia/New Zealand |
| <b>Portfolio</b>             | CommScope®            |
| <b>Product Type</b>          | Fiber OSP cable       |
| <b>Product Series</b>        | O-N3                  |

## General Specifications

|                          |            |
|--------------------------|------------|
| <b>Cable Type</b>        | Loose tube |
| <b>Subunit Type</b>      | Gel-filled |
| <b>Jacket Color</b>      | Black      |
| <b>Jacket Marking</b>    | Meters     |
| <b>Total Fiber Count</b> | 48         |

## Dimensions

|                             |                    |
|-----------------------------|--------------------|
| <b>Diameter Over Jacket</b> | 10.9 mm   0.429 in |
|-----------------------------|--------------------|

## Material Specifications

|                        |       |
|------------------------|-------|
| <b>Jacket Material</b> | Nylon |
|------------------------|-------|

## Mechanical Specifications

|             |           |
|-------------|-----------|
| <b>Flex</b> | 25 cycles |
|-------------|-----------|

## Optical Specifications

|                   |     |
|-------------------|-----|
| <b>Fiber Type</b> | OS2 |
|-------------------|-----|

## Optical Specifications, Wavelength Specific

|                             |                   |
|-----------------------------|-------------------|
| <b>Standards Compliance</b> | TIA-492CAAB (OS2) |
|-----------------------------|-------------------|

## Environmental Specifications

**Operating Temperature** -10 °C to +70 °C (+14 °F to +158 °F)

**Environmental Space** Buried

## Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b>  |
|---------------|--|
| CHINA-ROHS    | Below maximum concentration value  |
| REACH-SVHC    | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS          | Compliant  |
| UK-ROHS       | Compliant  |



## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable