RR-FA2-A



Fast Access RRU Mount Kit for Back-to-Back (B2B) Mounting of (2) RRUs to Round, Straight or Tapered members. With interface plate

The RR-FA2-A is a fast access remote radio mount bracket.

It is designed to provide a secure and efficient mounting solution for remote radio head units.

The RR-FA2 mount bracket features a revolutionary key hole located on the clamp that allows the radio and mount bracket assembly to slide perfectly into the clamp keyhole and relieves the operator from equipment weight load.

The new EZ Install design allows the brackets to be mounted to the radio prior to installation on the tower, and painlessly installed onto the tower reducing the chance of damage.

Supports all typical RRH units from Ericsson, Nokia, Samsung, Huawei, Fujitsu

RR-FA2-A includes (2) univeral adpater plate "860677769-001" for Ericsson ERS radios such as 8843, 4449, 4890, 4490, 8863

Product Classification

Portfolio CommScope®

Product TypeRemote radio head unit mount

Ordering Note CommScope® standard product with terms

Warranty One year

General Specifications

Mounting Round and angle legs

Radio Compatibility, Ericsson (2) RRUS11/12/32, 2212, 4415, 4426,

4478 | 4415 | 4426 | 4435 | 4449 | 4455 | 4460 | 4467 | 4478 | 4480 | 4490 | 4890 | 88

Radio Compatibility Samsung RF4402D-D1A | RF4437D | RF4439D | RF4440D | RF4442D | RFV01U-D1A | RFV01U-D2A | RT2201

48A | RT8808-77A

Tower Taper Non-tapered | Tapered

Dimensions

Height 416.56 mm | 16.4 in

Page 1 of 2



RR-FA2-A

Length 457.2 mm | 18 in

Mounting Diameter 2, maximum 152.4 mm | 6 in

Mounting Diameter 2, minimum 38.1 mm | 1.5 in

Mounting Diameter, maximum 142.24 mm | 5.6 in

Mounting Diameter, minimum 60.96 mm | 2.4 in

Material Specifications

Material Type Hot dip galvanized steel

Packaging and Weights

Included Clamps | Hardware

Packaging quantity 1

Weight, net 16.329 kg | 36 lb

* Footnotes

Warranty For more information, please consult our Product Warranty guidelines

