

# MTC40231255

---



Dual Universal Ring Mount (MC-RM1550-3D), 15 in to 50 in OD with (3) 4-1/2"OD x 63" Pipes

## Product Classification

**Product Type** Universal ring mount

## General Specifications

**Mounting** Monopole, 381–1270 mm (15–50 in) OD

**Pipe, quantity** 3

**Sectors, quantity** 3

## Dimensions

**Height** 1,600.2 mm | 63 in

**Mounting Diameter, maximum** 1270 mm | 50 in

**Mounting Diameter, minimum** 381 mm | 15 in

**Pipe Outer Diameter** 114.3 mm | 4.5 in

## Material Specifications

**Material Type** Hot dip galvanized steel

## Mechanical Specifications

**Wind Rating Test Method** TIA/EIA-222

## Packaging and Weights

**Included** Plain end pipes (3) | Ring mounts (2) | Threaded rod | U-bolts

**Weight, net** 316.925 kg | 698.7 lb