

TES-SS-PLK7 | MONOPOLE COLLAR MOUNT ASSEMBLY



Collar / Ring Mount for 12" to 45" OD Monopoles with 6" x 6" x 5/8" bolt pattern

Product Classification

Product Type Universal ring mount

General Specifications

Pipe, quantity 0

Sectors, quantity 3

Dimensions

Mounting Diameter, maximum 45 in | 1,143 mm

Mounting Diameter, minimum 12 in | 304.8 mm

Material Specifications

Material Type Hot dip galvanized steel

Packaging and Weights

Included Ring mount | Threaded rod

Packaging quantity 1