


FD3-AC144J00TBBP2-US



FDH 3000 Fiber Distribution Extra Small Pole Mount Cabinet, 72F, SC /APC, 0 splitters, die. LT, 96F stubs, 100 ft, 12F, Build America Buy America (BABA)

- *CommScope intends to release this product at a future date. At such time, this product will comply with the requirements of the Build America, Buy America Act and/or applicable waivers. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

Product Classification

Regional Availability	North America
Product Type	Fiber distribution hub
Product Series	FDH 3000
Government Funding	Build America Buy America (BABA) coming soon*

General Specifications

Access	Front
Cable Type	Dry Dielectric - Ribbon
Color	Putty white
Distribution Cables, quantity	1
Distribution Ports, quantity	144
Fibers per Distribution Cable, quantity	144
Fibers per Feeder Cable, quantity	24
Interface, Input	SC
Interface Feature, Input	APC
Mounting	Pole

Dimensions

Height	762 mm 30 in
Width	533 mm 20.984 in
Depth	356 mm 14.016 in
Cable Length	30.48 m 100 ft
Enclosure Size	Extra small

FD3-AC144J00TBBP2-US

Material Specifications

Finish	Powder coated
Material Type	Aluminum

Environmental Specifications

Environmental Space	Aerial
----------------------------	--------

Packaging and Weights

Packaging quantity	1
Packaging Type	Pallet

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

