

F4R-HPHMHF-1M



HELIAX® 1/2" Superflexible Fire retardant series SureFlex® Jumper with interface types 4.3-10 Male and 4.3-10 Female, 1 m, with black non-halogenated fire retardant polyolefin jacket

- WARNING: DO NOT MATE WITH 4.1-9.5 DIN

Product Classification

Product Type	SureFlex® HP, HELIAX® performance
Product Brand	HELIAX® SureFlex®
Product Series	RSJ4-50

General Specifications

Body Style, Connector A	Straight
Body Style, Connector B	Straight
Interface, Connector A	4.3-10 Male
Interface, Connector B	4.3-10 Female
Specification Sheet Revision Level	A

Dimensions

Length	1 m 3.281 ft
Nominal Size	1/2 in

Electrical Specifications

3rd Order IMD Static Test Method	Two +43 dBm carriers
3rd Order IMD, typical	-119 dBm
DTF, Connector A	-34 dB
DTF, Connector B	-34 dB

VSWR/Return Loss

Frequency Band	VSWR, typical	Return Loss, typical (dB)
680–960 MHz	1.065	30
1700–2200 MHz	1.065	30
2200–2700 MHz	1.083	28

F4R-HPHMHF-1M

3400-3800 MHz

1.222

20

Jumper Assembly Sample Label



Environmental Specifications

EN50575 CPR Cable EuroClass Fire Performance	B2ca
EN50575 CPR Cable EuroClass Smoke Rating	s1a
EN50575 CPR Cable EuroClass Droplets Rating	d1
EN50575 CPR Cable EuroClass Acidity Rating	a1
Immersion Test Method	Meets IEC 60529:2001, IP68 in mated condition