

760169177 | 360G2-iP-1U-32-MPO-DP-UHD

SYSTIMAX 360™ iPatch® G2 1U 32-MPO Distribution Panel, UHD Panel



OBSOLETE

Replaced By:

760169144 360G2-iP-1U-32-MPO-DP-SD	SYSTIMAX 360™ iPatch® G2 1U 32-MPO Distribution Panel, Sliding Panel
760217463 HD-iP-1U-32-MPO-DP-SD	HD iPATCH 1U 32-MPO Distribution Panel, Sliding Panel

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber splice panel
Product Brand	LazrSPEED® SYSTIMAX 360™ iPatch®

General Specifications

Color	Black
Intelligence Type	iPatch® enabled
Interface, front	MPO
Rack Units	1
Shelf Movement	Fixed
Total Ports, quantity	32

Dimensions

Height	44.45 mm 1.75 in
Width	482.6 mm 19 in
Depth	492.76 mm 19.4 in

Material Specifications

Material Type Acrylonitrile butadiene styrene (ABS) | Polycarbonate (PC)

Optical Specifications

Fiber Mode Multimode | Singlemode

Environmental Specifications

Operating Temperature -5 °C to +50 °C (+23 °F to +122 °F)

Storage Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Relative Humidity Up to 95%, non-condensing

Flammability Rating UL 94 V-0

Safety Standard Austel | CE | CSA | UL

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system

