



HighBand® 12-module Kit, category 6A, 20-pair modules

## Product Classification

<b>Regional Availability</b>	Australia/New Zealand
<b>Product Type</b>	Back mount frame kit
<b>Product Brand</b>	HighBand®
<b>Product Series</b>	HighBand®

## General Specifications

<b>ANSI/TIA Category</b>	6A
<b>Modules, quantity</b>	12
<b>Mounting</b>	Backmount frames
<b>Pairs, quantity</b>	240
<b>Termination Punchdowns, minimum</b>	200 times
<b>Termination Tool</b>	LSA-PLUS Punchdown tool
<b>Termination Type</b>	IDC
<b>Transmission Standards</b>	IEEE 802.3an   TIA/EIA-568 Cat 6A

## Dimensions

<b>Compatible Conductor Gauge, solid</b>	26–22 AWG
<b>Compatible Conductor Gauge, stranded</b>	26–22 AWG

## Electrical Specifications

<b>Current Rating, maximum</b>	2.5 A
<b>Insulation Resistance, minimum</b>	50 MΩ
<b>Safety Voltage Rating</b>	150 Vac

## Material Specifications

<b>Contact Plating Material</b>	Silver
---------------------------------	--------

# 64501107-01 | 6450 1 107-01

---

## Mechanical Specifications

**Plug Insertion Life, minimum** 750 times

## Environmental Specifications

**Environmental Space** Indoor | Outdoor

**Flammability Rating** UL 94 V-0

**Safety Standard** UL 1863

## Packaging and Weights

**Included** Label holder | Rear cable management

**Packaging quantity** 1

**Packaging Type** Box | Carton

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

