



Standard Density 1U sliding Panel, accepts (3) LGX/1000 style splice cassettes, modules or panels, providing up to 36 duplex LC ports

OBSOLETE

This product was discontinued on: October 31, 2022

Replaced By:

760249997	EPX 1U sliding panel, accepts (3) LGX/PNL style splice cassettes, modules or panels, providing up to 36 duplex LC ports
EPX-1U-PNL-ENC	

Product Classification

Portfolio	CommScope®
Product Type	Fiber patch panel
Product Series	SD

General Specifications

Application	Accepts three LGX/1000 footprint panels/cassettes
Color	Black
Interface, front	Unloaded
Rack Units	1
Shelf Movement	Sliding
Total Ports, quantity	0

Dimensions

Height	44.45 mm 1.75 in
Width	482.6 mm 19 in
Depth	474.98 mm 18.7 in

Material Specifications

Material Type	Acrylonitrile butadiene styrene (ABS) Polycarbonate (PC) Steel
----------------------	--

Environmental Specifications

Flammability Rating UL 94 V-0

Packaging and Weights

Packaging quantity 1

Weight, net 6.35 kg | 14 lb

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

