

# R57412-000 | OCMF-DMB1361L1

---

OCMF LGX Fiber Optic Module, DWDM, Mux, LC/UPC, 8 channels, starting wavelength 1567.13 nm

## Product Classification

<b>Regional Availability</b>	North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	DWDM module
<b>Product Series</b>	LGX   OCMF

## General Specifications

<b>Device Type</b>	Standard VAM
<b>Functionality</b>	Multiplexing
<b>Application</b>	For use with OMX frames
<b>Circuits, quantity</b>	1
<b>Distribution Type</b>	8-channel DWDM
<b>Interface, Input</b>	LC/UPC
<b>Interface, Output</b>	LC/UPC
<b>Multiplexers, quantity</b>	1
<b>Port Type, optional</b>	Upgrade port

## Dimensions

<b>Height</b>	131.06 mm   5.16 in
<b>Width</b>	16 mm   0.63 in
<b>Depth</b>	162.05 mm   6.38 in

## Optical Specifications

<b>Channel Spacing</b>	100 GHz
<b>Starting Wavelength</b>	1,548.51 nm

## Packaging and Weights

<b>Packaging quantity</b>	1
<b>Packaging Type</b>	Box   Carton

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

