

## FPS-D1JJ1QAA2AD1X PNP 40-CH, ITU 20-59

- Rugged packaging is built for high performance, while the Plug-and-Play design reduces installation time
- Bend-optimized fiber and ruggedized extreme temperature cabling
- Easy to insert and remove without affecting adjacent splitters
- Reversible dust cap makes test and turn-up easy

## Product Classification

<b>Regional Availability</b>	Latin America   North America
<b>Product Type</b>	DWDM module
<b>Product Series</b>	FDH 3000   Mini FDH 3000

## General Specifications

<b>Device Type</b>	Plug-and-play module
<b>Functionality</b>	Demultiplexing   Multiplexing
<b>Access</b>	Front   Rear
<b>Application</b>	For use in FDH 3000 cabinets
<b>Circuits, quantity</b>	1
<b>Distribution Type</b>	40-channel DWDM
<b>Interface Feature, Input</b>	Standard
<b>Interface Feature, Output</b>	Standard
<b>Interface, Input</b>	SC
<b>Interface, Output</b>	SC
<b>Module Color</b>	Black
<b>Multiplexers, quantity</b>	1

## Dimensions

<b>Height</b>	88.9 mm   3.5 in
<b>Width</b>	38.1 mm   1.5 in
<b>Depth</b>	139.7 mm   5.5 in

## Environmental Specifications

<b>Operating Temperature</b>	-55 °C to +85 °C (-67 °F to +185 °F)
<b>Qualification Standards</b>	Telcordia GR-1209-CORE   Telcordia GR-1221-CORE   Telcordia GR-326-CORE

## Packaging and Weights

**Packaging quantity** 1

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted

