

# 760244928 | G2-SP-24LCX-RPT

---



G2 Splice Cassette, 24LC with internal shutters, OM4, with ribbon pigtails

## Product Classification

|                              |   |
|------------------------------|---|
| <b>Regional Availability</b> | Asia   Australia/New Zealand   EMEA   Latin America   North America |
| <b>Portfolio</b>             | CommScope®  |
| <b>Product Type</b>          | Fiber cassette with ribbon pigtail                                  |
| <b>Product Series</b>        | G2  |

## General Specifications

|                               |                 |
|-------------------------------|-----------------|
| <b>Color, front</b>           | Aqua            |
| <b>Interface, front</b>       | LC/UPC          |
| <b>Interface, rear</b>        | Ribbon pigtail  |
| <b>Polarity</b>               | Pairs, straight |
| <b>Shuttered</b>              | Yes             |
| <b>Total Fibers, quantity</b> | 24              |

## Dimensions

|               |                      |
|---------------|----------------------|
| <b>Height</b> | 26.416 mm   1.04 in  |
| <b>Width</b>  | 96.52 mm   3.8 in    |
| <b>Depth</b>  | 165.354 mm   6.51 in |

## Material Specifications

|                                  |          |
|----------------------------------|----------|
| <b>Alignment Sleeve Material</b> | Zirconia |
|----------------------------------|----------|

## Optical Specifications

|                                |           |
|--------------------------------|-----------|
| <b>Fiber Mode</b>              | Multimode |
| <b>Fiber Type</b>              | OM4       |
| <b>Insertion Loss, maximum</b> | 0.15 dB   |

**Return Loss, minimum** 35 dB

## Environmental Specifications

**Qualification Standards** IEC 61753-1 | TIA-568.3-D

**Safety Standard** UL

## Packaging and Weights

**Included** SMOUV holder | SMOUV splice protection

**Packaging quantity** 1

**Weight, net** 0.123 kg | 0.271 lb

## Regulatory Compliance/Certifications

| Agency     | Classification  |
|------------|---|
| CHINA-ROHS | Below maximum concentration value   |
| REACH-SVHC | Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS       | Compliant   |
| UK-ROHS    | Compliant   |

