


Fiber boxes


At a glance

VERTICAL MDU SOLUTIONS

BUDI-2S




BUDI-1S




BUDI-S




BUDI-M




FOWB





MOBI



MOBI



COMMON FEATURES	Best application	Building entrance Single operator	Building entrance Single operator	Building entrance Single operator	Building entrance Single operator	Building entrance Single operator	Building entrance Operator box Multi operator	Building entrance Customer box Multi operator
	Indoor/outdoor	IP54	IP54	IP54	IP54	IP20	IP54	IP54
	Outer size (H X W X D)	285x155x60 mm	420x240x120 mm	500x295x145 mm	550x360x175 mm	220x140x35 mm	183x456x155 mm	183x456x155 mm
	Splice capacity - single element	36	96	168	216	×	×	×
SPLICED	Splice capacity - single circuit	12	32	56	72	×	×	×
	Cable loop	×	✓	✓	✓	×	×	×
	Splice capacity - single element	48	48	144	144	24	×	×
CONNECTORIZED	Splice capacity - single circuit	12	16	48	48	3-7 mm	×	×
	Cable loop	×	✓	✓	✓	N/A	×	×
	SC connections	8	16	24	up to 48	12	×	×
	LC connections	12	32	48	72	24	×	×
PLUG-AND-PLAY	Splitter modules	×	×	4 OCM6	6 OCM6	×	3 OCM7	×
	SC connections	×	×	24	up to 96	×	48	48
	LC connections	×	×	48	96	×	×	48
	Cable loop	×	×	×	✓	×	✓	✓

CABLING		BEST APPLICATION	INDOOR/OUTDOOR	FIBER COUNT	CABLE DIAMETER	PRE-TERMINATED	CONNECTORS
		Mini-breakout 	Building entrance to floor	Indoor	12/24	8,2 mm	Possible
Mini-bundle 	Building entrance to floor	Indoor	48/72/96	8,2/9/11 mm	Splicing only	×	

Fiber boxes

At a glance

HORIZONTAL MDU SOLUTIONS

	IFDB-S	IFDB-M	IFDB-PNP	COWO	HFTP	
COMMON FEATURES	Best application	Floor box	Floor box	Floor box	Wall outlet	
	Indoor/outdoor	Indoor	Indoor	Indoor	Indoor	
	Pass through	✓	✓	✓	✗	✗
SPliced	Splice capacity	4	16	✗	✗	✗
	Main cable diameter	10,5 mm	11 mm	✗	✗	✗
	Drop cable diameter	5 mm	6 mm	✗	✗	✗
	Outer size (H x W x D)	80x80x35mm	200x126x50mm	✗	✗	✗
CONNECTORIZED	Splice capacity	4	8	✗	2	4
	Main cable diameter	10,5mm	9 mm	✗	3-7 mm	up to 6 mm
	Drop cable diameter	5 mm	6 mm	✗	✗	✗
	SC connections	2	8	✗	2	2
	LC connections	✗	✗	✗	2	4
Outer size (H x W x D)	80x80x35 mm	216x126x50 mm	✗	115x80x24,5 mm	105,5x82,5x23,8 mm	
PLUG-AND-PLAY	Splitter modules	✗	✗	1	✗	✗
	Main cable diameter	✗	✗	11	✗	✗
	SC connections	✗	✗	up to 8	✗	✗
	LC connections	✗	✗	✗	✗	✗
	Outer size (H x W x D)	✗	✗	125x125x55 mm	✗	✗

		BEST APPLICATION	INDOOR/OUTDOOR	FIBER COUNT	PRE-TERMINATED	CONNECTORS	COATING
CABLING	PICO	Horizontal cabling	Indoor	1	Possible	SC/LC	Secondary
	RICO	Horizontal cabling	Indoor	1/2/4	Possible	SC/LC	Jacketed