



HGS620 M-Series Adapter, Black (25 ea/pkg)

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Adapter
<b>Ordering Note</b>	Minimum order quantity, 20 packs

## General Specifications

<b>Color</b>	Black
<b>Integrated Dust Cover Type</b>	None

## Dimensions

<b>Height</b>	17.53 mm   0.69 in
<b>Width</b>	18.54 mm   0.73 in
<b>Depth</b>	9.14 mm   0.36 in

## Material Specifications

<b>Material Type</b>	High-impact, flame retardant, thermoplastic
----------------------	---

## Environmental Specifications

<b>Operating Temperature</b>	-10 °C to +60 °C (+14 °F to +140 °F)
<b>Storage Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Flammability Rating</b>	UL 94 V-0
<b>Safety Standard</b>	UL   cUL

## Packaging and Weights

<b>Packaging quantity</b>	25
---------------------------	----

## Regulatory Compliance/Certifications

**Agency**

ISO 9001:2015  
REACH-SVHC  
ROHS  
UK-ROHS

**Classification**

Designed, manufactured and/or distributed under this quality management system  
Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)  
Compliant  
Compliant