

760237427 | 26" Pole Cab with Round Shaft



Bottom of the Pole, 26in Square 4G/5G capable Concealment Enclosure to house and conceal multiple low to high power radios and any other wireless infrastructure equipment in a cabinet at the base of the pole.

- Intended to house and conceal multiple radios and any other wireless infrastructure equipment in a cabinet at the base of the pole
- Pole top concealment module for LAA/CBRS radio mounting
- Flexible configuration accepts low to high-power single or dual band radios, Integrated AC load center/OVP and Disconnect and integrated AC/DC rectifier options

Available with Pole Top concealment, mmWave 5G mounting, luminaire arms.

OBSOLETE

Replaced By:

760240957
30" Pole Cab with Round Shaft

Bottom of the Pole, 30in Square 4G/5G capable Concealment Enclosure to house and conceal multiple low to high power radios and any other wireless infrastructure equipment in a cabinet at the base of the pole.

Product Classification

Product Type	Pole cab
Product Brand	Metro Cell
Ordering Note	ANDREW® standard product with terms
Warranty	One year

General Specifications

Color	Light Gray (RAL 7035)
Color Options	Beige-Grey (RAL 7006) Black (RAL 9005) Black Green (RAL 6012) Brown (RAL 8014) Faux Concrete Green (RAL 6005) Metallic Silver Umbra Grey (RAL 7022) White (RAL 9010)
Compatible Foundation Type	Poured Concrete Pre-Cast Concrete
Compatible Smart Devices	Cameras Digital Signage Emergency Call Station Environmental Monitoring Security Lighting WIFI
Cooling	Fan Cooling
Power Supply Compatibility	ABB CC1600 CCI PSU-1200W-48-N DELTA 2.0 PSU-AC-08
Radio Compatibility, Ericsson	(1) 8843/4449 dual-band high power radio and (2) PSU-AC08 220x 440x Power Distribution

760237427 | 26" Pole Cab with Round Shaft

Radio Compatibility, Nokia AHFIA | AHFIB | AHIA | AHIB | AHLBA | AHLBBA | AZRB | Airscale micro | Power Distribution

Radio Compatibility Samsung Power Distribution | RF4402D-D1A | RT2201-46A | RT4401-48A

Radios Included None

Dimensions

Height Note 4 ft tall Equipment Cabinet Base

Pole Height Options 10.668 m | 35 ft | 12.192 m | 40 ft | 6.096 m | 20 ft | 7.62 m | 25 ft | 9.144 m | 30 ft

Width 660.4 mm | 26 in

Depth 660.4 mm | 26 in

Depth Note Square

Pole Diameter 203.2 mm | 8 in

Electrical Specifications

Power/Fiber Input AC load center with OVP and disconnect

Material Specifications

Finish Aluminum Chromate

Finish Concealment Covers Powder coated

Material Type Steel

Environmental Specifications

Thermal Compliance GR-487