

760243184 | 18" Multi Carrier Integrated Pole



Multi Carrier Round 18 inch diameter, Integrated Pole Base Concealment Pole for 4G/5G deployments, to house and conceal multiple radios and any other wireless infrastructure equipment in the base of the pole.

- Intended to house and conceal multiple radios and any other wireless infrastructure equipment in a cabinet at the base of the pole
- Includes everything needed for a low-power 4G/5G outdoor small cell site
- Base of 18in diameter accepts low power radios or mid-power dual band radios
- Concealment integrates AC load center/OVP and disconnect

Capable of supporting Multiple Carriers

Product Classification

Product Type	Integrated pole
Product Brand	Metro Cell
Ordering Note	ANDREW® standard product with terms
Warranty	One year

General Specifications

Antenna Compatibility, ANDREW	ANDREW Canister Antennas
Antenna Compatibility, Other Vendors	ACE AMPHENOL GALTRONICS GAMMA NU JMA KATHREIN KMW ROSENBERGER
Antennas Included	None
Color	Light Gray (RAL 7035)
Color Options	Beige-Grey (RAL 7006) Black (RAL 9005) Black Green (RAL 6012) Brown (RAL 8014) Faux Concrete Green (RAL 6005) Metallic Silver White (RAL 9010)
Compatible Foundation Type	Poured Concrete Pre-Cast Concrete
Compatible Smart Devices	Cameras Digital Signage Emergency Call Station Environmental Monitoring Security Lighting WIFI
Cooling	Fan Cooling
Power Supply Compatibility	ABB CC1600 APAF DELTA 2.0 FPAE
Radio Compatibility, Ericsson	(12) 2203/2205/2208 radios (2) 2212/4415/4426/4478 and (2) Ericsson PSU AC08 (3) 2205/2208 (Pole Top) 220x 440x 4415 4426 4478 6701 6705
Radio Compatibility, Nokia	(8) Airscale micro radios (Base) AHFIA AHIA AHIB AZRB
Radio Compatibility Samsung	AT1K01 AT1K02 RF4402D-D1A RT2201-46A RT4401-48A

760243184 | 18" Multi Carrier Integrated Pole

Radios Included None

Dimensions

Height Note 10 ft tall Equipment Base | 3.5 ft tall Radio Expansion Module

Pole Height Options 10.668 m | 35 ft | 12.192 m | 40 ft | 6.096 m | 20 ft | 7.62 m | 25 ft | 9.144 m | 30 ft

Depth 457.2 mm | 18 in

Depth Note Round

Pole Diameter 203.2 mm | 8 in

Electrical Specifications

Power/Fiber Input AC load center with OVP and disconnect

Material Specifications

Finish Aluminum Chromate

Finish Concealment Covers Powder coated

Material Type Steel

Environmental Specifications

Thermal Compliance GR-487