


FE-12104-ETM-R4



Hybrid Junction box, 4 RRUs, 1 External hybrid trunk connection, 4 Internal hybrid jumper connections, Field installable, Mounting kit included

OBSOLETE

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Outdoor junction box

General Specifications

Application	Used as a fiber/power junction box
Cable Entry, quantity, maximum, bottom	4
Color	Gray
Mounting	Pipe, 44–114 mm (1.75–4.5 in) OD Wall

Dimensions

Height	254 mm 10 in
Width	304.8 mm 12 in
Depth	101.6 mm 4 in
Cable Entry Jumper Gland Size, maximum	18 mm 0.709 in
Cable Entry Jumper Gland Size, minimum	13 mm 0.512 in

Material Specifications

Material Type	High-impact polycarbonate, UV resistant
----------------------	---

Environmental Specifications

Operating Temperature	-40 °C to +75 °C (-40 °F to +167 °F)
Environmental Space	Indoor Outdoor
Qualification Standards	IEC 60529:2001, IP67

FE-12104-ETM-R4

Packaging and Weights

Included	Mounting kit
Weight, net	1.579 kg 3.48 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

