

760248104 | ODF-SPLCAB-12



UMSC (Universal Mounted Splice Cabinet) with up to 3456 fiber splices capacity (Rollable ribbon cables), exit up, gray, splice trays are not included

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Product Type	Universal Mounted Splice Cabinet
Product Series	Flex Frame

General Specifications

Access	Front
Cable Entry Location	Top
Cable Exit Location	Top
Color	Gray
Growth Configuration	Unloaded
Mounting	Back to Back Rack, EIA 19 in Rack, EIA 23 in Wall
Splice Trays Included, quantity	0
Splicing Capacity Note	Up to 3456 Rollable ribbon splice
Splicing Capacity, maximum	3456

Dimensions

Height	1,074.2 mm 42.291 in
Width	430 mm 16.929 in
Depth	287.9 mm 11.335 in

Environmental Specifications

Environmental Space	Indoor
----------------------------	--------

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value

760248104 | ODF-SPLCAB-12

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

