399274-000 | OCC1P-20800-L2SESEB



OCC1P Wideband Splitter, planar, singlemode, 2x8, symmetrical split ratio, LC/APC, 0.9 mm cable, medium duty housing

Product Classification

Regional Availability EMEA | Latin America | North America

Product Type Splitter component

Product Series OCC1P

General Specifications

Device Type Component, rectangular

Functionality Splitting

Technology Type Planar lightwave circuit (PLC)

Application For use in FOSC closures

Circuits, quantity 1

Distribution Type 2 x 8 splitter

 Interface, Input
 LC

 Interface Feature, Input
 APC

 Interface, Output
 LC

 Interface Feature, Output
 APC

Split Ratio Symmetrical

Splitter, quantity 1

Dimensions

Pigtail Length, Input1.5 m | 4.921 ftPigtail Length, Output1.5 m | 4.921 ftPigtail Diameter, Input0.9 mm | 0.035 inPigtail Diameter, Output0.9 mm | 0.035 in



399274-000 | OCC1P-20800-L2SESEB

Environmental Specifications

Qualification Standards Telcordia GR-1209-CORE | Telcordia GR-1221-CORE

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant

